

Non-contact Infrared Thermometer for Human beings
MODEL NO. HF110



APPLICATION

Special Used for Human Beings, high-precision, high Stability.

KEY FEATURES

- Distance Spot Ratio: 1~10cm
- Resolution: 0.1°C 0.1°F
- Response Time: 1~2 sec & 8-14um
- Repeatability: $\pm 0.1^{\circ}\text{C}$
- °C/°F Selection
- Inner/Surface Convert
- Auto Power Off
- Color back light indication
- Data hold function
- The default setting is green back light. When temperature reach alert limit, it will turn to red back light.
- Alarm function: The alert limit of the alarm function is 37.5°C as default. When the reading reaches 37.5°C, the buzzer will ring with " Bi, Bi, Bi" sound and the back light will turn red.

Non-contact Infrared Thermometer for Human beings MODEL NO. HF110

SPECIFICATIONS

* Temperature Range:

Body inner: 34 °C~ 45°C(93.2°F to 113°F),When less than 34°C,display"LO",When over 45°C,display"HI"

Ambient operation range : 0 °C~ 40°C(32°F to 104°F)

* Accuracy:±0.2°C(testing environment temperature 23°C,±3°C)

* Distance Spot Ratio: 1~10cm

* Emissivity: 0.95 pre-set

* Resolution:0.1°C, 0.1°F

* Response Time: 1~2 sec & 8-14um

* Repeatability: ±0.1°C

* °C/°F Selection

* Inner/Surface Convert

* Auto Power Off

* Color back light indication

* Data hold function

* The default setting is green back light. When temperature reach alert limit, it will turn to red back light.

* Alarm function: The alert limit of the alarm function is 37.5°C as default. When the reading reaches 37.5°C, the buzzer will ring wiht"Bi,Bi,Bi" sound and the back light will turn red.



ACCESSORIES

* Instruction Manual x 1pc

* 9V battery x 1pc

* Blister packing



BESTONE INDUSTRIAL LTD.

Tel: +86 755 82952326, Fax: +86 755 82952326

Web: www.bestone-meter.com

Email: liu@bestone-meter.com

Skype: Bestone-Shirley Liu

WhatsApp: +86 18929394326